0.6W Single-Frequency Nd:YVO₄/BiB₃O₆ Laser at 671nm

Fabíola Camargo^{2*}, Thomas Zanon-Willette¹, Thomas Badr¹, Niklaus Ursus Wetter² and Jean-Jacques Zondy¹

Abstract: Using a Nd:YVO₄ ring laser and a type-I critically phase-matched BiBO crystal, a record 620 mW single-frequency red laser at 671.2nm is demonstrated. The laser is tunable over $\Delta\lambda$ ~1.2nm around 671 nm.

© 2009 Optical Society of America

OCIS codes: (140.3570) Lasers, single-mode; (190.2620) Frequency conversion

Single-frequency cw lasers in the visible region are very interesting for high precision spectroscopy as alternative to dye lasers. A laser source emitting at 671nm is necessary to laser cool Lithium atoms on the $^2S_{1/2}$ – $^2P_{1/2}$ dipolar transition and it could be achieved using intracavity second-harmonic generation of the 1342nm emission line of the Nd:YVO₄. Watt-level power diode-pumped frequency-doubled cw lasers were previously demonstrated at 671nm [1] but without spectral purity (i.e. single-longitudinal mode or SLM) or tunable operation. The largest SLM red power (370mW) was reported by Agnesi *et al* by using a standing-wave cavity in which the type-II cut LBO harmonic generator served also as a birefringent etalon [2]. In this work, in order to avoid hole-burning modes we employ a single-end longitudinally pumped, unidirectional ring resonator containing a type-I cut (θ =8.6°, ϕ =0°) BiB₃O₆ (BiBO) nonlinear crystal [3] to synthesize as much as 620 mW of single longitudinal mode (SLM) red output at 671nm, which is – to the best of our knowledge – the largest cw SLM red power obtained from such a Nd:YVO₄ laser.

A low-doped (0,15at%) 10 mm long Nd:YVO₄ crystal is used in order to decrease the thermal lens generated inside the crystal, resulting in \sim 90% absorbed fiber-coupled diode pump power at 808nm. A fused silica thin etalon with facets reflectivity of 40% is placed near the larger beam focus inside the cavity to minimize insertion loss. The unidirectional operation is obtained using a Brewster-cut TGG Faraday rotator and a zero-order half wave plate.

All mirrors are broadband HR-coated dichroic mirrors (R>99.8% in the range 1300-1350nm, with T~90% in the 650-810nm range). The near-IR power leaking through M3 is used for diagnostic purposes (wavelength measurement and spectral analysis by a confocal Fabry-Perot resonator with a FSR=750 MHz free spectral range). The BiBO crystal is placed between two curved mirrors at the smaller cavity waist.

At gain center a maximum SLM red output with 620mW is achieved without etalon (Fig.2b), owing to the self-suppression of longitudinal modes in a homogeneously broadened laser (higher loss experienced by sum frequency processes between longitudinal modes). This corresponds to an optical-to-optical efficiency η =6% at P_{abs} =10W of absorbed pump power. However smooth, stable and extended ($\Delta\lambda_{red} \sim 1.25$ nm) SLM wavelength tuning requires the insertion of the etalon at the expense of higher losses (Fig.2a).





Fig. 1: Diode end-pumped Nd:YVO₄/BiBO ring laser setup.






Fig. 2 : Single-frequency red output power versus wavelength (a), taken at P_{abs} =10W with the R=40% etalon, and versus absorbed pump power (b). Without etalon, SLM operation is characterized by frequent mode-hops.

References

[1] A.Y. Yao, W.Hou, X.C. Lin, Y. Bi, R.N. Li, D.F. Cui, Z.Y. Xu, "High power red laser at 671 nm by intracavity-doubled Nd: YVO4 laser using LiB3O5", Appl Opt 44, 7156-7160 (2005).

[2] A. Agnesi, G. C. Reali, P. G. Gobbi, "430-mW single-transverse-mode diode-pumped Nd:YVO₄ laser at 671 nm", IEEE J. Quantum Electron. **34**,1297-1300 (1998).

[3] R. Sarrouf, T. Badr, J.-J. Zondy, "Intracavity second-harmonic generation of diode-pumped continuous-wave, single-frequency 1.3 μm Nd:YLiF₄ lasers", J. Opt. A: Pure Appl. Opt. **10**, 104011(10pp) (2003).

¹Institut National de Métrologie, Conservatoire National des Arts et Métiers, 61 rue du Landy, F-93210 La Plaine Saint-Denis, France. ² Centro de Lasers e Aplicações, Instituto de Pesquisas Energéticas e Nucleares, Av. Lineu Prestes 2242, 005508-000 São Paulo, Brazil. *Corresponding author e-mail: facamargo@usp.br